

Interruptores termomagnéticos para Riel-Din Serie SH200 (Curva C)

SH200 Tripolares (Curva C, Im= 5 a 10 In)



SH203

Referencia para pedido	Interruptor termomagnético (3 polos, curva C)	Corriente nominal In (A)	Corriente nominal de ruptura Icn (KA) según norma IEC 60898 230 VAC	Cantidad por caja	Valor referencial unitario S/
2CDS213001R0024	Mini Circuit Breaker SH203 C2 6kA	2	10	4	141.00
2CDS213001R0044	Mini Circuit Breaker SH203 C4 6kA	4	10	4	146.00
2CDS213001R0064	Mini Circuit Breaker SH203 C6 6kA	6	10	4	128.00
2CDS213001R0104	Mini Circuit Breaker SH203 C10 6kA	10	10	4	94.00
2CDS213001R0164	Mini Circuit Breaker SH203 C16 6kA	16	10	4	94.00
2CDS213001R0204	Mini Circuit Breaker SH203 C20 6kA	20	10	4	94.00
2CDS213001R0254	Mini Circuit Breaker SH203 C25 6kA	25	10	4	94.00
2CDS213001R0324	Mini Circuit Breaker SH203 C32 6kA	32	10	4	100.00
2CDS213001R0404	Mini Circuit Breaker SH203 C40 6kA	40	10	4	105.00
2CDS213001R0504	Mini Circuit Breaker SH203 C50 6kA	50	10	4	126.00
2CDS213001R0634	Mini Circuit Breaker SH203 C63 6kA	63	10	4	139.00

SH200 Tetrapolares (Curva C, Im= 5 a 10 In)



SH204

Referencia para pedido	Interruptor termomagnético (4 polos, curva C)	Corriente nominal In (A)	Corriente nominal de ruptura Icn (KA) según norma IEC 60898 230 VAC	Cantidad por caja	Valor referencial unitario S/
2CDS214001R0024	Mini Circuit Breaker SH204 C2 6kA	2	10	3	201.00
2CDS214001R0044	Mini Circuit Breaker SH204 C4 6kA	4	10	3	207.00
2CDS214001R0064	Mini Circuit Breaker SH204 C6 6kA	6	10	3	183.00
2CDS214001R0104	Mini Circuit Breaker SH204 C10 6kA	10	10	3	169.00
2CDS214001R0164	Mini Circuit Breaker SH204 C16 6kA	16	10	3	115.00
2CDS214001R0204	Mini Circuit Breaker SH204 C20 6kA	20	10	3	115.00
2CDS214001R0254	Mini Circuit Breaker SH204 C25 6kA	25	10	3	136.00
2CDS214001R0324	Mini Circuit Breaker SH204 C32 6kA	32	10	3	136.00
2CDS214001R0404	Mini Circuit Breaker SH204 C40 6kA	40	10	3	140.00
2CDS214001R0504	Mini Circuit Breaker SH204 C50 6kA	50	10	3	224.00
2CDS214001R0634	Mini Circuit Breaker SH204 C63 6kA	63	10	3	236.00

Para mayor información
escanea el código QR

